

R⊕\S Imao







| Body                  | O-Ring             |
|-----------------------|--------------------|
| A5052 aluminum<br>Red | NBR nitrile rubber |

| Part Number | D    | Н    | D <sub>1</sub> | М      | Weight (g) | Bushing     |             |
|-------------|------|------|----------------|--------|------------|-------------|-------------|
| CP735-0939P | 13.5 | 15   | 9              | M4×0.7 | 3          | CP735-0939L | CP735-0939S |
| CP735-1246P | 17   | 19   | 12             |        | 6          | CP735-1246L | CP735-1246S |
| CP735-1656P | 23   | 22.5 | 16             | M5×0.8 | 14         | CP735-1656L | CP735-1656S |

## How To Use

## ■How to Install

Insert the product to the center hole of the Flex Locator Bushings and use it as a protective cover.

## ■How to Remove

Insert a screw into the tapped hole and pull it out.

